








REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 300V AC.DC
 - 2. Rated current: 7A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0(2)
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME:		TITLE: 3.96 mm Pitch Connector Housing			
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DL39613 (SLP)-2Y		PART NO:			
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:21.10.10	SCALE: N/A			
FINISH:		CHKD: Wu Hui	DATE:21.10.10	PAGE: 1/1		REV.: B	
DRAWING NO:		APPD:Ren An De	DATE:21.10.10	UNITS: mm			




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 300V AC/DC
 - 2. Rated current: 7A AC/DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0(2)
 - 8. Matched RoHS criteria

Circuits	PRODUCT NAME	Dimension mm	
		A	B
2	SLP-2Y	3.96	9.16
3	SLP-3Y	7.92	13.12
4	SLP-4YM	11.88	17.08


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DL39613 (SLP)-Y		3.96 mm Pitch Connector Housing	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	DR: Chen Quan Long	DATE: 21.10.10	PART NO:	
FINISH:		CHKD: Wu Hui	DATE: 21.10.10	SCALE: N/A	
DRAWING NO:		APPD: Ren An De	DATE: 21.10.10	UNITS: mm	PAGE: 1/1
				REV.: B	



REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 300V AC.DC
 - 2. Rated current: 7A AC DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0(2)
 - 8. Matched RoHS criteria


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME:	TITLE: 3.96 mm Pitch Connector Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:21. 10. 10
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DATE:21. 10. 10	PART NO:
FINISH:		CHKD: Wu Hui	DATE:21. 10. 10
DRAWING NO:		APPD:Ren An De	DATE:21. 10. 10
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV. : B




NOTES:

1. Rated voltage: 300V AC/DC
2. Rated current: 7A AC/DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temperature: $-40^\circ\text{C} \sim +105^\circ\text{C}$
7. Material: Nylon UL94V-0(2)
8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^\circ$	PRODUCT NAME:		TITLE: 3.96 mm Pitch Connector Housing	
.XX: ± 0.15	.X°: $\pm 2.0^\circ$	DL39613 (SLP) -6Y		PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^\circ$	DR: Chen Quan Long	DATE: 21.10.10	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE: 21.10.10	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 21.10.10	UNITS: mm	REV.: B






REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 300V AC/DC
 - 2. Rated current: 7A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0(2)
 - 8. Matched RoHS criteria



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME:	TITLE: 3.96 mm Pitch Connector Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DL39613 (SLP)-1R	
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR: Chen Quan Long	DATE: 21.10.10
FINISH:		CHKD: Wu Hui	DATE: 21.10.10
DRAWING NO:		APPD: Ren An De	DATE: 21.10.10
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: B




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 300V AC.DC
 - 2. Rated current: 7A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0(2)
 - 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME:	TITLE: 3.96 mm Pitch Connector Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DL39613 (SLP)-2R	
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:21.10.10
FINISH:		CHKD: Wu Hui	DATE:21.10.10
DRAWING NO:		APPD:Ren An De	DATE:21.10.10
			SCALE: N/A
			PAGE: 1/1
			UNITS: mm
			REV.: B



CIRCUIT NO. 1




NOTES:

1. Rated voltage: 300V AC/DC
2. Rated current: 7A AC/DC
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 1500V AC/minute
6. Ambient temperature: $-40^\circ\text{C} \sim +105^\circ\text{C}$
7. Material : Nylon UL94V-0(2)
8. Matched RoHS criteria

Circuits	PRODUCT NAME	Dimension mm	
		A	B
2	SLP-2R	3.96	9.16
3	SLP-3R	7.92	13.12
4	SLP-4RM	11.88	17.08


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^\circ$	PRODUCT NAME: DL39613 (SLP)-R	TITLE: 3.96 mm Pitch Connector Housing
.XX: ± 0.15	.X°: $\pm 2.0^\circ$	DR: Chen Quan Long	DATE: 21.10.10
.XXX: ± 0.01	.XX°: $\pm 1.0^\circ$	DATE: 21.10.10	PART NO:
FINISH: —		CHKD: Wu Hui	DATE: 21.10.10
DRAWING NO:		APPD: Ren An De	DATE: 21.10.10
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: B



REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 300V AC.DC
 - 2. Rated current: 7A AC DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0(2)
 - 8. Matched RoHS criteria


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
. X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME:	TITLE: 3.96 mm Pitch Connector Housing
. XX: ± 0.15	. X° : $\pm 2.0^{\circ}$	DL39613 (SLP) -4R	
. XXX: ± 0.01	. XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:21. 10. 10
FINISH:		CHKD: Wu Hui	DATE:21. 10. 10
DRAWING NO:		APPD:Ren An De	DATE:21. 10. 10
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV. : B



REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 300V AC/DC
 - 2. Rated current: 7A AC/DC
 - 3. Contact resistance: ≤20 mΩ
 - 4. Insulation resistance: ≥1000 MΩ
 - 5. Withstand voltage: 1500V AC/minute
 - 6. Ambient temperature: -40℃~+105℃
 - 7. Material : Nylon UL94V-0(2)
 - 8. Matched RoHS criteria


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE: 3.96 mm Pitch Connector Housing	
.XX: ± 0.15	.X° : ± 2.0°	DL39613 (SLP) -6R			
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21.10.10	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:21.10.10		
DRAWING NO:		APPD:Ren An De	DATE:21.10.10	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV.: B



REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
1. Rated voltage: 300V AC.DC
 2. Rated current: 7A AC DC
 3. Contact resistance: ≤20 mΩ
 4. Insulation resistance: ≥1000 MΩ
 5. Withstand voltage: 1500V AC/minute
 6. Ambient temprature: -40℃~+105℃
 7. Material : Nylon UL94V-0(2)
 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:	TITLE: 3.96 mm Pitch Connector Housing
.XX: ± 0.15	.X° : ± 2.0°	DL39613 (SLP)-8R	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21.10.10
FINISH:		CHKD: Wu Hui	DATE:21.10.10
DRAWING NO:		APPD:Ren An De	DATE:21.10.10
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: B




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 300V AC/DC
Rated current: 7A AC/DC
Contact resistance: ≤20 mΩ
Insulation resistance: ≥1000 MΩ
Withstand voltage: 1500V AC/minute
Ambient temperature: -40℃ ~ +105℃
Wire range: AWG#26~#18
Materials:
Terminal: Phosphor bronze, Tin plated

TYPE	Dimension mm				Applicable wires
	A1	B1	A2	B2	AWG#
SLP-RT	3.7	3.5	2.6	2.5	22-18
SLP-RT-D	3.7	3.3	2.4	2.1	26-20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL39613 (SLP)-RT	TITLE: 3.96 mm Pitch Wire To Wire Crimp Terminal
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE: 21.10.10
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE: 21.10.10
FINISH:		APPD: Ren An De	DATE: 21.10.10
DRAWING NO:		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 300V AC/DC
Rated current: 7A AC/DC
Contact resistance: ≤20 mΩ
Insulation resistance: ≥1000 MΩ
Withstand voltage: 1500V AC/minute
Ambient temperature: -40℃~+105℃
Wire range: AWG#26~#18
Materials:
Terminal: Phosphor bronze, Tin plated

TYPE	Dimension mm				Applicable wires
	A1	B1	A2	B2	AWG#
SLP-T	3.7	3.5	2.6	2.5	22-18
SLP-T-D	3.7	3.3	2.4	2.1	26-20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL39613 (SLP)-T		TITLE: 3.96 mm Pitch Wire To Wire Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:21.10.10	PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:21.10.10	SCALE: N/A	PAGE: 1/1
FINISH:		APPD:Ren An De	DATE:21.10.10	UNITS: mm	REV.: A
DRAWING NO:					