








RoHS2.0+REACH


NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	PBT UL94V-0	BLACK	1




P/N: 3GY01-P19010-A2001 (X KEYING)



P/N: 3GY01-P19010-A2002 (Y KEYING)



3D VIEW FOR X KEYING



3D VIEW FOR Y KEYING

NOTE(UNLESS OTHERWISE SPECIFIED):
1. ALL MATERIAL MUST BE COMPLY WITH ROHS+REACH.
2. PRODUCT PERFORMANCE:
2.1 RATED VOLTAGE(MAX.):250V AC/DC
2.2 RATED CURRENT(MAX.):7.0A AC/DC(24AWG)
2.3 DIELECTRIC STRENGTH:1500V AC/MINUTE
2.4 INSULATION RESISTANCE:1000 MΩ MIN.
2.5 CONTACT RESISTANCE:10 mΩ MAX.
2.6 OPERATING TEMPERATURE:-55°C TO +105°C
3.APPLICABLE WIRE: CONDUCTOR SIZE/ AWG #24 TO #28
INSULATION O.D./ 0.8 TO 1.4mm
4.PART NO. : 3GY01- P19010-A200X
WATER CODE
010:10PIN

DRAWING:
ShunMingWen

CHECKED:
TianHai

APPROVAL:
Cykin

GENERAL TOLERANCE


.X:=±0.30 .X':=±2"
.XX:=±0.20 .XX':=±1"
.XXX:=±0.10 .XXX':=±0.5"

UNIT: MM

SCALE: 1:1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION: 10PIN FEMALE HOUSING(3.81mm PITCH)

PART NO: SEE NOTES

OLD CODE:

DRAWING NO: UK0632

REV: 1.0

SIZE: A4

2.0			
1.0	09/25.24	NEW	ShunMingWen
NO.	DATE	DESCRIPTION	DRAWING