






RoHS



NOTE(UNLESS OTHERWISE SPECIFIED):

1. ALL MATERIAL MUST BE COMPLY WITH ROHS.

2. PRODUCT PERFORMANCE:

2.1 RATED VOLTAGE(MAX.):15V AC/DC

2.2 RATED CURRENT(MAX.):1.5A AC/DC




2.3 DIELECTRIC STRENGTH:500V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN

2.4 INSULATION RESISTANCE:1000 MΩ MIN. 500VDC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL

2.5 CONTACT RESISTANCE:30 mΩ MAX.

2.6 OPERATING TEMPERATURE:-40° to +85°

3.PART NO. LEGEND: 1SA07-141022-00001



RECOMMENDED P.C.B LAYOUT

6.0	22.03.10	1. 修订品号 2. 更新图框	ZQH
5.0	16.01.29	R角部位增加管控	Tian hai
4.0	15.12.20	依客户要求修订尺寸管控	Tian hai
3.0	15.10.26	追加尺寸管控	Tian hai
2.0	14.12.02	追加LAYOUT视图	Xiaoyong
1.0	14.09.04	NEW	Xiaoyong
REV.	DATE	DESCRIPTION	DRAWING

DRAWING:	GENERAL TOLERANCE
Bains	.X:=±0.30 .X':=±2°
CHECKED:	.XX:=±0.20 .XX':=±1°
Tianhai	.XXX:=±0.10 .XXX':=±0.5°
APPROVAL:	UNIT: MM PROJECTION:
Cykin	SCALE: 1/1
	SHEET: 1/1

CHIN-BAN
Electronic Technology

DESCRIPTION:	SATA 7+15 成品图	
PART NO:	1SA07-141022-00001	REV: 6.0
DRAWING NO:	UK0097	SIZE: A4