







RoHS2.0+REACH


NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	PBT UL94V-0	BLACK	1

NOTE(UNLESS OTHERWISE SPECIFIED):
1. ALL MATERIAL MUST BE COMPLY WITH ROHS+REACH.
2. PRODUCT PERFORMANCE:
2.1 RATED VOLTAGE(MAX.):250V AC/DC
2.2 RATED CURRENT(MAX.):7.0A AC/DC(24AWG)
2.3 DIELECTRIC STRENGTH:1500V AC/MINUTE
2.4 INSULATION RESISTANCE:1000 MΩ MIN.
2.5 CONTACT RESISTANCE:10 mΩ MAX.
2.6 OPERATING TEMPERATURE:-55°C TO +105°C
3.APPLICABLE WIRE: CONDUCTOR SIZE/ AWG #24 TO #28
INSULATION O.D./ 0.8 TO 1.4mm


4.PART NO. : 3GY01- U19003-A200X
2001:X KEYING
2002:Y KEYING
2003:Z KEYING
003:3PIN




P/N: 3GY01-U19003-A2001 (X KEYING)




3D VIEW FOR X KEYING




P/N: 3GY01-U19003-A2002 (Y KEYING)



3D VIEW FOR Y KEYING



P/N: 3GY01-U19003-A2003 (Z KEYING)



3D VIEW FOR Z KEYING

DRAWING:
ShunMingWen

CHECKED:
TianHai


APPROVAL:
Cykin

GENERAL TOLERANCE
.X:=±0.30 .X*:=±2°
.XX:=±0.20 .XX*:=±1°
.XXX:=±0.10 .XXX*:=±0.5°

UNIT: MM

PROJECTION:

SCALE: 1:1



SHEET: 1/1

HIN-BAN
Electronic Technology

DESCRIPTION: 3PIN FEMALE HOUSING(5.08mm PITCH)

PART NO: SEE NOTES

REV: 1.0

OLD CODE:

DRAWING NO: UG0712

SIZE: A4

2.0			
1.0	09/25.24	NEW	ShunMingWen
NO.	DATE	DESCRIPTION	DRAWING