





2 Pin



3 Pin以上



SPECIFICATIONS


- 1、Material: Nylon66 UL94-V0(2)
- 2、Color: Nature

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-SM-2YS-05	2.50	5.50
3	HC-SM-3YS-05	5.00	7.50
4	HC-SM-4YS-05	7.50	10.00
5	HC-SM-5YS-05	10.00	12.50
6	HC-SM-6YS-05	12.50	15.00
7	HC-SM-7YS-05	15.00	17.50
8	HC-SM-8YS-05	17.50	20.00
9	HC-SM-9YS-05	20.00	22.50
10	HC-SM-10YS-05	22.50	25.00
11	HC-SM-11YS-05	25.00	27.50
12	HC-SM-12YS-05	27.50	30.00

Ordering Information

HC-SM - N*** - * - 05

Pin Type Colour
YS-线锁扣
EYS-线锁扣
默认-本色
R-红色
L-蓝色
B-黑色
Y-黄色
P-紫色
G-绿色
W-白色
GR-灰色

			GENE RL TOLERANCE	制 图 DRAWING		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	SM (2.50) 线锁扣	版 本 REV.	A
1	初版发行		X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	HC-SM-NYS-05	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X.XXX ±0.10	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						