

A

B

C

D

1

2

3

4

5


REV.	ECN	DESCRIPTION	MDF'D		DATE	
		新订图面				
孔位 Poles	型号 (Type)	A	B	C	D	
2	GH-2Y	1.25	2.0	3.75	---	
3	GH-3Y	2.5	3.0	5.0	---	
4	GH-4Y	3.75	4.2	6.25	---	
5	GH-5Y	5.0	4.2	7.5	---	
6	GH-6Y	6.25	6.2	8.75	---	
7	GH-7Y	7.5	6.2	10.0	8.7	
8	GH-8Y	8.75	6.2	11.25	8.7	
9	GH-9Y	10.0	6.2	12.50	8.7	
10	GH-10Y	11.25	8.2	13.75	10.7	
11	GH-11Y	12.50	8.2	15.0	10.7	
12	GH-12Y	13.75	8.2	16.25	10.7	
13	GH-13Y	15.0	8.2	17.5	10.7	
14	GH-14Y	16.25	8.2	18.75	10.7	
15	GH-15Y	17.5	8.2	20.0	10.7	
16	GH-16Y	18.75	8.2	21.25	10.7	
18	GH-18Y	21.25	8.2	23.75	10.7	

A




B

C

D




线型：1571 28#



技术要求:

- 标识清晰可见，表面不得有划痕，裂纹，起
泡，污损，毛刺等；
- 无明显影响使用功能和接触性能的缺陷
- 材料：塑料PA66
- 额定电流：0.5A AC,DC
- 额定电压：30V AC,DC
- 接触电阻： $\leq 20m\Omega$
- 绝缘电阻： $\geq 100M\Omega$
- 应用线型：AWG #28 (1571)
- 温度范围：-25℃ to +85℃



深圳市韩下电子有限公司

品名 (ITEM NO)	HX GH1.25-3P ST 200mm 28AWG
料号 (PART NO)	
图号 (DWG NO)	

页码 (SHEET)	1	单位 (UNIT) : MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2024.3.20	 未注公差 TOLERANCE UNSPECIFIED
设计 (DESIGN)	黄彬	
审核 (CHECKED)	张伟	
核准 (APPROVED)	罗小春	