

1






2

3

4

5

REV.	ECN	DESCRIPTION		MDF'D	DATE
		新订图面			



Poles	Part No	Dimensions mm	
		A	B
2	PH-2Y	2.00	5.80
3	PH-3Y	4.00	7.80
4	PH-4Y	6.00	9.80
5	PH-5Y	8.00	11.80
6	PH-6Y	10.00	13.80
7	PH-7Y	12.00	15.80
8	PH-8Y	14.00	17.80
9	PH-9Y	16.00	19.80
10	PH-10Y	18.00	21.80
11	PH-11Y	20.00	23.80
12	PH-12Y	22.00	25.80
13	PH-13Y	24.00	27.80
14	PH-14Y	26.00	29.80
15	PH-15Y	28.00	31.80
16	PH-16Y	30.00	33.80
---	---	---	---

技术要求:

- 标识清晰可见，表面不得有划痕，裂纹，起泡，污损，毛刺等；
- 无明显影响使用功能和接触性能的缺陷
- 材料：塑料PA66
- 额电电流：1.0A AC, DC
- 额电电压：300V AC, DC
- 接触电阻： $\leq 20m\Omega$
- 绝缘电阻： $\geq 100M\Omega$
- 应用线型：AWG #24 (1007)
- 温度范围：-25°C to +85°C

	深圳市韩下电子有限公司	页码 (SHEET)	1	单位 (UNIT) : MM
		版本 (REV)	A1	比例 (SCALE) 1:1
品名 (ITEM NO)	HX PH2.0-4P ST 200mm 24AWG	日期 (DATE)	2024.3.20	
料号 (PART NO)		设计 (DESIGN)	黄彬	未注公差 TOLERANCE UNSPECIFIED
图号 (DWG NO)		审核 (CHECKED)	张伟	> XX ±3 > X ±1 0.X ±0.20 0.XX ±0.15
		核准 (APPROVED)	罗小春	

尺寸范围	>0-3	>3-18	>18-50	>50-120
公差	±0.15	±0.2	±0.35	±0.5

1

2

3

4

5