






符合RoHS环保要求

装吸取盖示意图



- 备注:**
1. 材质:
 - 1.1 胶芯: LCP+30%G.F UL94V-0
 - 1.2 端子: 高导铜C7025/C2680; 镍底50μ" MIN, 接触区镀镍金(AU 1u") 焊接区镀镍金G/F
 - 1.3 外壳: SUS201/SUS304, T=0.30mm(表面镀镍50μ" MIN)
 - 1.4 中夹片: SUS304
 2. 主要特性:
 - 2.1 额定电流: 3A/5A
 - 2.2 接触阻抗: 40mΩ MAX (初始值)
50mΩ MAX (测试后)
 - 2.3 绝缘阻抗: 100MΩ MIN
 - 2.4 耐压测试: 100V AC R.M.S.
 - 2.6 整体插入力: 5-20N 整体插入力: 5-20N (耐久后)
整体拔出力: 6-20N 整体拔出力: 6-20N (耐久后)
 - 2.7 耐久: 10000次
 - 2.8 耐高温: SMT回流焊 (峰值260° ±5°), 塑胶不能有起泡, 熔胶等不良, 变色, 翘曲变形在公差范围以内
 - 2.9 品须做焊锡测试, 粘锡面积达到95%以上
 - 3.0 盐雾测试: 24H MIN/48H MIN
 - 3.1 工作温度: -30°C~+85°C



| TOLERANCE | | NAME (INTENDED USE) | | CUSTOMER DRAWING | |
|-----------|-------|---------------------|------|------------------|--------------------|
| X.X | ±0.30 | X. | ±10° | PART NO. | FY23-124TC42476-01 |
| .XX | ±0.20 | X° | ±8° | | |
| .XXX | ±0.10 | XX° | ±5° | DESIGN: | ZXM |
| UNITS | mm | | | DRAWG NO. | |
| MATERIAL | — | CHEM: | | | FY23-024TC42476-01 |
| FINISH | — | APPD: | | SCALE | SHEET REV. |

RECOMMENDED P.C.B. LAYOUT (1:1.00mm)

TOLERANCE UNSPECIFIED ±0.05mm

| | | | |
|-------|---|----------------------------------|--|
| FUYOU | 广东富盈兴业精密科技实业有限公司 Guangdong Fuyou Precision Electronic Technology Co., Ltd. | TITLE: TYPE C 24p母座立贴.0脚长.0.95带弹 | |
| | | DRAWG NO. | |