





L=200mm



线型：1007 22#



REV.	ECN	DESCRIPTION	MDF'D	DATE
		新订图面		

技术要求:

1. 标识清晰可见, 表面不得有划痕, 裂纹, 起泡, 污损, 毛刺等;
2. 无明显影响使用功能和接触性能的缺陷
3. 材料: 塑料PA66
4. 额电电流: 1.5A AC, DC
5. 额电电压: 300V AC, DC
6. 接触电阻: $\leq 20\text{m}\Omega$
7. 绝缘电阻: $\geq 100\text{M}\Omega$
8. 应用线型: AWG #22 (1007)
9. 温度范围: -25°C to $+85^\circ\text{C}$

编 号	尺寸 (mm)	
	A	B
XH25401-02Y	2.50	7.50
XH25401-03Y	5.00	10.00
XH25401-04Y	7.50	12.50
XH25401-05Y	10.00	15.00
XH25401-06Y	12.50	17.50
XH25401-07Y	15.00	20.00
XH25401-08Y	17.50	22.50
XH25401-09Y	20.00	25.00
XH25401-10Y	22.50	27.50
XH25401-11Y	25.00	30.00
XH25401-12Y	27.50	32.50
XH25401-20Y	47.50	52.50



® 深圳市韩下电子有限公司

页码 (SHEET)	1	单位 (UNIT): MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2024.3.20	○
设计 (DESIGN)	黄彬	未注公差 TOLERANCE UNSPECIFIED
审核 (CHECKED)	张伟	> XX ± 3 > X ± 1 0.X ± 0.20 0.XX ± 0.15
核准 (APPROVED)	罗小春	