


材质及电镀
焊针：黄铜，镀锡
塑件：PA66 UL94V-0
电气性能
额定电压：300V
额定电流：12A
接触电阻：20m
绝缘电阻：5000/1000V
耐电压：AC1500V/1min
机械性能
温度范围：-40 ° C~+105 ° C
瞬时温度：+250 ° C 5秒



		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	2EDGRC-5.08-XXP	UNLESS OTHERWISE		X. ±0.25		
			MODEL NAME	2EDGRC-5.08-XXP	SPECIFIED,TOLERANCE:		X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15			
							ANGULAR	±3°	
								FILE.NO.	