



SECTION A-A
SCALE 1:1



Recommended P.C.B. Layout
Unspecified tolerance: ± 0.05
(Top view)




A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME


UK I A A T C C B
⊢ ⊢ ⊢ ⊢ ⊢ ⊢ ⊢
⊙ ⊙ ⊙ ⊙ ⊙ ⊙ ⊙
(A) (B) (C) (D) (E) (F) (G) (H)

A.Series: Type-C Female
B.Specification: 16 Pin
C.Mounting Method: Vertical Plug-in
D.Dimensions: H6.5mm
E.Type: General Type
F.Material: SUS
G.Service Life: 10,000 Cycles
H.Product Code: B50

成品	内壳		SUS304R-1/2H.T=0.30mm	Ni:50u"Min;
	MD半成品	叠料	中夹片	Ni:50u"Min;
			上排 MD	C2680R-H. T=0.15mm 端子
		下排 MD	C7025 TM03. T=0.15mm 端子	SOLDE AREA: G/F.
	塑胶料	LCP(G.F30%) BLACK.	/	
MATERIALS				FINISH



FIRST VIEW



The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.

WWW.KKK-JP.COM

TITLE::	TYPE-C 16P立插DIP母座 H=6.5MM 5A
---------	------------------------------

of DWG NO: UKIA16-P0006

PART NO: UKIA24070318

MODEL NO: UKIAATCCB

NAME:	TYPE-C CONN
-------	-------------

GENERAL TOLERANCE

 ± 0.15

DESIGN	WANGGUIFA	2018.06.12	$\geq 2 \sim 5 <$	$+0.25$
--------	-----------	------------	-------------------	---------

CHECKED	ZHENGUILAN	2018.06.12	$\geq 0 \sim 2 <$	± 0.15
---------	------------	------------	-------------------	------------

APPROVED	LILIANJIANG	2018.06.14	≥ 5	+0.35
----------	-------------	------------	----------	-------

SAMZO COMPONENTS
Electronic switch and connector manufacturer