












MATERIALS AND FINISH
SHELL : STEEL MATERIAL, NICKEL FINISHED
INSULATOR : PBT THERMOPLASTIC, 30% GLASS
FILLED, UL 94V-0 RATED, BLACK COLOR
CONTACT MATERIAL: BRASS
CONTACT FINISH : FULL GOLD FLASHED
GROUNDING BRACKET : BRASS MATERIAL, TIN
FINISHED
ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING : 5.0 AMPS
CONTACT RESISTANCE : 30 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN
INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
TEMPERATURE RATING : -55°C ~ +105°C




DMR-XXPF-XX
TYPE



PIN

F:Female M:Male
Color:W:white B:black



TYPE-5

No. of Contact	A±0.20	B ±0.20	C±0.20	D			new		2015/5/3		A		瀚源
					ECN BO.		DESCRIPTION.		DATE.		REV.		
09	30.90	24.99	16.34	11.08	DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1
15	39.24	33.32	24.76	19.30	Mikey	Tom	Jerry	PART NAME	DMR-XXPF-XX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25
25	53.10	47.04	38.40	33.24				MODEL NAME	DMR-XXPF-XX			X.x	±0.20
37	69.50	63.50	54.89	49.86				3RD ANGLE PROJ	HanElectricity Co.,LTD		FILE.NO.		X.xx
												ANGULAR	±3°