



2.5±0.2

SEC:A-A



SEC:B-B



SEC:C-C

技术指标(Technical Index) :

1. 工作温度(Temperature range): -25° C~85° C.
2. 额定电压(Rated voltage): 250V DC/AC(rms).
3. 额定电流(Rated current): 2.0A.
4. 接触电阻(Contact resistance): ≤30mΩ.
5. 耐压值(Dielectric withstand voltage): 1000V AC/minute.
6. 绝缘电阻(Insulation resistance): ≥1000MΩ.
7. 适用线规(Apply to gauge): AWG#28 to 24.

RoHS

一般公差(TOLERANCE)
X. ±50 .XX ±10
X ±20 .XXX ±.05
ANGLES ±1°

品名 (TITLE)	501646公头端子	制图 (DR)	ANLAN
料号 (DWG.NO)		校对 (CHKD)	田峰
		审核 (APPD)	黄志明
比例 (SCALE)	单位 (UNITS) mm	张数 (SHEET) 1 OF 1	SIZE A4
		REV A	