







TYPE-1




TYPE-4




TYPE-2



TYPE-5



TYPE-3



PARTS DIMENSION TABLE			
parts no.	DIM. a	DIM. b	inner thread
1	4.8	11.8	4#40
2	5.8	12.0	4#40
3	4.8	11.8	M3
4	5.8	11.8	M3
5	4.8	11.8	M2.6
6	5.8	12.0	M2.6
7	6.0	12.0	4#40

MATERIALS AND FINISH

SHELL : STEEL MATERIAL, NICKEL FINISHED
DIMPLES ON PLUG ONLY

INSULATOR : PBT THERMOPLASTIC, 30% GLASS
FILLED, UL 94V-0 RATED, BLACK COLOR

CONTACT MATERIAL : BRASS

CONTACT FINISH : SELECTIVE GOLD FLASH

GROUNDING BRACKET : BRASS MATERIAL, TIN FINISHED

JACK SCREWS : STEEL MATERIAL , NICKEL FINISHED
WITH #4-40 THREADED ASSEMBLED

ELECTRICAL CHARACTERISTICS

CONTACT CURRENT RATING : 5.0 AMPS

CONTACT RESISTANCE : 30 MILLIOHMS MAX.

DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC MIN.

INSULATION RESISTANCE : 5000 MEGAOHMS MIN.

TEMPERATURE RATING : -55°C ~ +105°C

DMR-XXPM-XX

TYPE

PIN

F:Female M:Male

Color:W:white B:black

No. of Contact	A ±0.20	B ±0.20	C ±0.20	D	_____		new		2015/5/3		A	瀚源
					ECN BO.		DESCRIPTION.		DATE.		REV.	
09	30.90	24.99	16.95	11.08	DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2	SCALE: 3:1
15	39.24	33.32	25.38	19.30	Mikey	Tom	Jerry	PART NAME	DMR-XXPM-XX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25
25	53.10	47.04	38.86	33.24				MODEL NAME	DMR-XXPM-XX			X.x ±0.20
37	69.50	63.60	55.37	49.86				3RD ANGLE PROJ	HanElectricity Co.,LTD		ANGULAR ±0.15	
											FILE.NO.	