




REMARKS:
1.100%OPEN SHORT TEST
2.INXULATION RESISTANGE TEST:DC300V/20MΩ

2	IDC-20H(2) 1.27*1.27	2	PBT+G/F BLACK
1	FLC-20P PH=0.635mm	1	GRAYL=50mm
ITEM	DESCRIPTION	Q'TY	REMARK

DRAW:		TOLERANCE		东莞市扬展康电子有限公司 DONGGUAN YZCONN ELECTRONIC CO., LTD						
JUDY		SELECT					✓			
CHECK1:	ON / TOL	1	2							
	.XXX ±	0.05	0.10							
CHECK2:	.XX ±	0.15	0.20	PART NO:CL12720050YZ-001						
	.X ±	0.20	0.25							
APPD:	ANGLE ±	2°	3°				TITLE: 排线两端IDC1.27/20P L=50mm (不含头) 同向			
	DATE	2023. 10. 23								
				SCALE		UNIT				REV
				4 : 1		MM				B