






主要技术参数、性能

The Main Thchnology Performance

额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	≤100mΩ
按力 Operating force	±50gf
行程 Travel	0.20±0.10mm
绝缘电阻 Insulated resistance	≥100MΩ
介电强度 Dielectric strength	≥250VAC/1min



电路图

CIRCUIT DIAGRAM

PCB. 焊接图


PCB. WELDING DRAWING

E	按钮	PPA	1	黑色
D	盖板	铁	1	镀铜锡
C	弹片	不锈钢	1	镀银
B	本体	PPA	1	黑色
A	卡件	黄铜	1	镀银
项目 ITEM	名称 DESCRIPTION	材质 MATERIAL	数量 QTY	表面处理/颜色 FINISH/COLOR

F	2	J	***	*	*	1	0
<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>	<u> </u>
(A)	(B)	(C)	(D)	(E)	(F)	(G)	(H)

A. 系列:F-4. 5*4. 5mm
B. 贴装方式:2-卧式插件
C. 引脚规格:J-3PIN
D. 操作高度:035-3. 5/050-5. 0mm(3. 5-10. 0)
E. 操作力度:1-120/2-180/3-260gf
F. 操作寿命:1-10万/2-20万次
G. 固定方式:1-无住
H. 物料编码:0-常规

			GENERAL TOLERANCE	
			$\geq 0 \sim 2 <$	± 0.15
DESIGN	WANGGUIFA	2018.06.12	$\geq 2 \sim 5 <$	± 0.25
CHECKED	ZHENGUILAN	2018.06.12	$\geq 0 \sim 2 <$	± 0.15
APPROVED	LILIANJIANG	2018.06.14	≥ 5	± 0.35

FIRST VIEW						TITLE:	
The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM						4.5*4.5*H 边三脚 卧式插件	
SCALE	1:1	UNIT	mm			DWG NO: F2J000-P044	
						PART NO:F2J1661440	
SAMZO COMPONENTS Electronic switch and connector manufacturer						MODEL NO:F2J-***-*-10	
							NAME:
							TACT SWITCH