





序号	名 称	规 格 说 明	数量
1	端 子	IDC-20P 三件式 (2.54mm)	1
1	端 子	IDC-20P 三件式 (2.54mm)	1
2	电 线	2651 28# 1.27间距灰排 7/0.12TS	20

DRAW:	JUDY	TOLERANCE		东莞市扬展康电子有限公司 DONG GUAN YZCONN ELECTRONIC CO., LTD					
		SELECT	✓						
CHECK1:		ON TOL	1	2	PATE NO: CL2542320HCX-07				
		.XXX±	0.05	0.10					
CHECK2:		.XX±	0.15	0.20	TITLE: 灰排线两端IDC2.54/20P 三件式 L=100+5 (不含头)				
		.X±	0.20	0.25					
APPD:		ANGLE±	2°	3°			SCALE	UNIT	REV
		DATE	2024. 04. 10				4 : 1	MM	B