







PCB线路板安装图(±0.1)

Technical drawing of a mechanical part with dimensions: 6.5, 4.0±0.2, 1, 0.3, 2.5, and L±0.2.

8.35	9.5	03.2
7.85	9.0	03.2
7.35	8.5	03.3
6.85	8.0	03.3
6.35	7.5	03.3
5.85	7.0	03.3
5.35	6.5	03.3
4.85	6.0	03.3
4.35	5.5	03.3
3.85	5.0	03.5
3.15	4.3	03.5
高度L 单位 (mm)	帽头H 单位 (mm)	直径A 单位 (mm)



1. 使用温度: $-25^{\circ}\text{C} \sim +65^{\circ}\text{C}$;
2. 额定负荷: DC 12V 50mA;
3. 接触电阻: $\leq 50\text{m}\Omega$;
4. 绝缘电阻: $\geq 100\text{M}\Omega$;
5. 耐 压: AC250V(50Hz)/min;
6. 动作力: $160\text{g} \pm 50\text{g}$;
7. 使用寿命: 100000次;
8. 未注尺寸公差参照下表格。

5	接触脚	黄铜	镀银	1	
4	底座	PPA(黑色)	————	1	
3	支架	黄铜	铜锡	1	
2	簧片	不锈钢	镀银	1	
1	按钮	PPA(黑色)	————	1	
序号	零件名称	材料规格	表面处理	数量	备注

额定电流、电压 Rate voltage,current	50mA DC12V
接触电阻 Contact resistance	$\leq 100\text{m}\Omega$
按力 Operating force	$\pm 50\text{gf}$
行程 Travel	$0.25 \pm 0.10\text{mm}$
绝缘电阻 Insulated resistance	$\geq 100\text{M}\Omega$
介电强度 Dielectric strength	$\geq 250\text{VAC}/1\text{min}$

			GENERAL TOLERANCE	
			$\geq 0 \sim 2 <$	± 0.15
DESIGN	WANGGUIFA	2018.06.12	$\geq 2 \sim 5 <$	± 0.25
CHECKED	ZHENGUILAN	2018.06.12	$\geq 0 \sim 2 <$	± 0.15
APPROVED	LILIANJIANG	2018.06.14	≥ 5	± 0.35

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

6.0*6.0mm 2支架 无固定脚

of DWG NO: M22K0351-P01

PART NO: M22K-03510

MODEL NO: M22K-***-*-11F5

TACT SWITCH

SAMZO COMPONENTS
Electronic switch and connector manufacturer