







1	2	3	4	5	6	7	8	9
							日期 DATE	ECN NO.
版本 REV.							变更内容 DESCRIPTION	制图 DRAWN

SPECIFICATIONS



1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperatuer Range: -25°C ~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000MΩ Min
 6. Withstanding Voltang: 1000V AC/minute
 7. Material:Wafer PA66, UL94V-0
- PIN Phosphor bronze Tin-plated



PCB LAYOUT



PIN	尺寸 (mm)		
	A	B	C
-02P	2.50	7.50	5.70
-03P	5.00	10.00	8.20
-04P	7.50	12.50	10.70
-05P	10.00	15.00	13.20
-06P	12.50	17.50	15.70
-07P	15.00	20.00	18.20
-08P	17.50	22.50	20.70
-09P	20.00	25.00	23.20
-10P	22.50	27.50	25.70
-11P	25.00	30.00	28.20
-12P	27.50	32.50	30.70



任何孔位第1针打K方向

GENERAL TOLERANCE	制图 Mapping	张迎春 2022. 09. 15	料号 PART NO.	KH-A25010-11P	版本 REV.	A
X.±0.25	X.°±2°	审核 Audit	钱岳生 2022. 09. 15	品名 TITLE	XH板对板直针 WAFER DIP TYPE	页次 SHEET
.X.±0.25	.X.°±1°	核 准 Approved	张名 2022. 09. 16	客户料号 CUTM. NO.		1/1
.XX±0.15	.XX°±0.5°					
.XXX±0.10	.XXX°±0.5°	单位 Units	mm	比例 SCALE		

深圳市金航标电子有限公司