




版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN






SPECIFICATIONS



- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer PA66, UL94V-0
PIN Phosphor bronze Tin-plated



PCB LAYOUT



PIN	尺寸 (mm)		
	A	B	C
-02P	2.50	7.50	5.70
-03P	5.00	10.00	8.20
-04P	7.50	12.50	10.70
-05P	10.00	15.00	13.20
-06P	12.50	17.50	15.70
-07P	15.00	20.00	18.20
-08P	17.50	22.50	20.70
-09P	20.00	25.00	23.20
-10P	22.50	27.50	25.70
-11P	25.00	30.00	28.20
-12P	27.50	32.50	30.70



任何孔位第1针打K方向

GENERL TOLERANCE		制 图 Mapping	张迎春 2022、09、15			料 号 PART NO.	KH-A25010-08P		版 本 REV.	A
X.±0.25	X.°±2°		钱岳生 2022、09、15			品 名 TITLE	XH板对板直针 WAFER DIP TYPE		页 次 SHEET	1/1
.X±0.25	.X°±1°	审 核 Audit	张 名 2022、09、16			客 户 料 号 CUTM. NO.	深圳市金航标电子有限公司			
.XX±0.15	.XX°±0.5°	核 准 Approved								
.XXX±0.10	.XXX°±0.5°	单 位 Units	mm	比 例 SCALE						