




1	2	3	4	5	6	7	8	9
A	B	C	D	E	F	G	A	A
							版本 REV.	日期 DATE
							ECN NO.	变更内容 DESCRIPTION
								制图 DRAWN








## SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C ~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer PA66,UL94V-0  
PIN Phosphor bronze Tin-plated



PCB LAYOUT



GENERAL TOLERANCE		制图 Mapping	张迎春 2022. 09. 15		料号 PART NO.	KH-A25010-06P	版本 REV.	A
X.±0.25	X.°±2°	审核 Audit	钱岳生 2022. 09. 15		品名 TITLE	XH板对板直针 WAFER DIP TYPE	页次 SHEET	1/1
.X.±0.25	.X.°±1°	核 准 Approved	张名 2022. 09. 16		客户料号 CUTM. NO.			
.XX.±0.15	.XX.°±0.5°							
.XXX.±0.10	.XXX.°±0.5°	单位 Units	mm	比例 SCALE				

深圳市金航标电子有限公司