








## SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperatuer Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000MΩ Min
6. Withstanding Voltang: 1000V AC/minute
7. Material:Wafer PA66, UL94V-0  
PIN Phosphor bronze Tin-plated



PCB LAYOUT



任何孔位第1针打K方向

GENERAL TOLERANCE		制图 Mapping	张迎春 2022. 09. 15		料号 PART NO.	KH-A25010-10PW		版本 REV.
X. ± 0.25	X. ° ± 2°	审核 Audit	钱岳生 2022. 09. 15		品名 TITLE	XH板对板弯针 WAFER DIP TYPE		页次 SHEET
.X. ± 0.25	.X. ° ± 1°	核 准 Approved	张名 2022. 09. 16		客户料号 CUTM. NO.			1/1
.XX. ± 0.15	.XX. ° ± 0.5°		单位 Units	mm	比例 SCALE			
.XXX. ± 0.10	.XXX. ° ± 0.5°							

深圳市金航标电子有限公司

版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN