







ECN NO.	REV	DATE	DESCRIPTION	DRAWN
	A0	2021/05/10	NEW	



- NOTES:
- 1.IMPEDANCE: 50 OHM NOMIAL
 - 2.FREQUENCY RANGE: DC-6 GHz
 - 3.TEMPERATURE RANGE: -40℃ TO +105℃
 - 4.MATING CYCLES: ≥25 CYCLES
 - 5.RETENTION FORCE LATCH: ≥110N



FKRM-1007-04x

X=CODE

NO.	Part name	Number	Material	Plating / Color	CODE	COLOR	CODE	COLOR
7						Black A		Violet H
6						White B		Beige I
5						Blue C		Curry K
4	Nonconductor 绝缘	1	PTFE	White		Bordeaux D		Camine Red L
3	Contact 中心针	1	Copper	Au		Green E		Pastel Orange M
2	Body主体	1	Copper	NI		Brown F		Pastel Green N
1	Housing外壳	1	PA/PBT	See table		Grey G		Waterblue Z

TOLERANCE OTHERWISE UNLESS SPECIFIED			UNIT
UNOVER 5±0.2	5~30±0.3	OVER 30±0.4	mm

COMPANY TRADEMARK		TYPE	FAKRA CONNECTOR		DRAWN	曾巩丽	深圳市金航标电子有限公司									
		MODEL NO	KH-FKRM-1007-04x		CHECKED	邹立发										
		VIEW		SCALE	APPROVED											
				A4 1:1	DATE	2021/05/10	DWG NO.	E	C	O	*	*	*	*	*	*