







| | | | | |
|------------|------------|---------|---------------------|-------------|
| 版本 REV. | 日期 DATE | ECN NO. | 变更内容 DESCRIPTION | 制图 DRAWN |
| | | | | |

SPECIFICATIONS



- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer PA66, UL94V-0
PIN Phosphor bronze Tin-plated



PCB LAYOUT



| PIN | 尺寸 (mm) | | |
|------|---------|-------|-------|
| | A | B | C |
| -02P | 2.50 | 7.50 | 5.70 |
| -03P | 5.00 | 10.00 | 8.20 |
| -04P | 7.50 | 12.50 | 10.70 |
| -05P | 10.00 | 15.00 | 13.20 |
| -06P | 12.50 | 17.50 | 15.70 |
| -07P | 15.00 | 20.00 | 18.20 |
| -08P | 17.50 | 22.50 | 20.70 |
| -09P | 20.00 | 25.00 | 23.20 |
| -10P | 22.50 | 27.50 | 25.70 |
| -11P | 25.00 | 30.00 | 28.20 |
| -12P | 27.50 | 32.50 | 30.70 |



任何孔位第1针打K方向

| | | | | | | | | |
|-------------------|------------|----------------|-------------------|-------------------|---------------------------|--|-------------|-----|
| GENERAL TOLERANCE | | 制图 Mapping | 张迎春 2022、09、15 | 料号 PART NO. | KH-A25010-10P | | 版本 REV. | A |
| X.±0.25 | X.°±2° | 审核 Audit | 钱岳生 2022、09、15 | 品名 TITLE | XH板对板直针 WAFER DIP TYPE | | 页次 SHEET | 1/1 |
| .X±0.25 | .X°±1° | 核准 Approved | 张名 2022、09、16 | 客户料号 CUTM. NO. | | | | |
| .XX±0.15 | .XX°±0.5° | 单位 Units | mm | 比例 SCALE | 深圳市金航标电子有限公司 | | | |
| .XXX±0.10 | .XXX°±0.5° | | | | | | | |