




| 版本<br>REV. | 日期<br>DATE | ECN NO. | 变更内容<br>DESCRIPTION | 制图<br>DRAWN |
|------------|------------|---------|---------------------|-------------|
|            |            |         |                     |             |






## SPECIFICATIONS



- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer PA66, UL94V-0  
PIN Phosphor bronze Tin-plated



## PCB LAYOUT



| PIN  | 尺寸 (mm) |       |       |
|------|---------|-------|-------|
|      | A       | B     | C     |
| -02P | 2.50    | 7.50  | 5.70  |
| -03P | 5.00    | 10.00 | 8.20  |
| -04P | 7.50    | 12.50 | 10.70 |
| -05P | 10.00   | 15.00 | 13.20 |
| -06P | 12.50   | 17.50 | 15.70 |
| -07P | 15.00   | 20.00 | 18.20 |
| -08P | 17.50   | 22.50 | 20.70 |
| -09P | 20.00   | 25.00 | 23.20 |
| -10P | 22.50   | 27.50 | 25.70 |
| -11P | 25.00   | 30.00 | 28.20 |
| -12P | 27.50   | 32.50 | 30.70 |



任何孔位第1针打K方向

| GENEERL TOLERANCE |            | 制 图<br>Mapping  | 张迎春<br>2022、09、15 |                   | 料 号<br>PART NO. | KH-A25010-03P     | 版 本<br>REV.               | A                                                                                     |     |
|-------------------|------------|-----------------|-------------------|-------------------|-----------------|-------------------|---------------------------|---------------------------------------------------------------------------------------|-----|
| X.±0.25           | X.°±2°     |                 | 审 核<br>Audit      | 钱岳生<br>2022、09、15 |                 | 品 名<br>TITLE      | XH板对板直针<br>WAFER DIP TYPE | 页次<br>SHEET                                                                           | 1/1 |
| .X±0.25           | .X°±1°     | 核 准<br>Approved |                   | 张 名<br>2022、09、16 |                 | 客户料号<br>CUTM. NO. |                           |  |     |
| .XX±0.15          | .XX°±0.5°  |                 | 单 位<br>Units      | mm                | 比 例<br>SCALE    | 深圳市金航标电子有限公司      |                           |                                                                                       |     |
| .XXX±0.10         | .XXX°±0.5° |                 |                   |                   |                 |                   |                           |                                                                                       |     |