








SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperatuuer Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000MΩ Min
6. Withstanding Voltang: 1000V AC/minute
7. Material:Wafer PA66, UL94V-0
PIN Phosphor bronze Tin-plated



PCB LAYOUT



任何孔位第1针打K方向

PIN	尺寸 (mm)		
	A	B	C
-02PW	2.50	7.50	5.70
-03PW	5.00	10.00	8.20
-04PW	7.50	12.50	10.70
-05PW	10.00	15.00	13.20
-06PW	12.50	17.50	15.70
-07PW	15.00	20.00	18.20
-08PW	17.50	22.50	20.70
-09PW	20.00	25.00	23.20
-10PW	22.50	27.50	25.70
-11PW	25.00	30.00	28.20
-12PW	27.50	32.50	30.70

GENERAL TOLERANCE	制图 Mapping	张迎春 2022. 09. 15	料号 PART NO.	KH-A25010-07PW	版本 REV.	A
X.±0.25	X.°±2°	审核 Audit	钱岳生 2022. 09. 15	品名 TITLE	XH板对板弯针 WAFER DIP TYPE	页次 SHEET
.X.±0.25	.X.°±1°	核 准 Approved	张名 2022. 09. 16	客户料号 CUTM. NO.		1/1
.XX.±0.15	.XX.°±0.5°					
.XXX.±0.10	.XXX.°±0.5°	单位 Units	mm	比例 SCALE		

深圳市金航标电子有限公司