


1. 产品尺寸图Product Dimension Drawing



2. 产品电器参数Product electrical parameters

防护等级 (Ingress protection)	IP50
插拔测试 (Plugging and unplugging test)	<500次
产品耐温 (The product is temperature resistant)	-20° C / +85° C
盐雾腐蚀 (Salt Spray Corrosion)	>48 hr
额定电流Current rating	5A
额定电压 (Rated voltage)	125V
工作电压 (AC.V)	200
Operating voltage (AC.V)	1500
耐电压 (AC.V)	1500
Withstand voltage (AC.V)	1500
绝缘阻抗 (mΩ) DC500V	1500
Insulation Resistance (mΩ)DC500V	5
绝缘电阻 (mΩ) DC1A	
Insulation Resistance (mΩ)DC1A	

3. 环境及表面处理产品特性Environmental and surface treatment product characteristics

外壳材料 Housing material	锌合金镀镍Zinc alloy nickel plating
绝缘体材料 Insulator material	橡胶黑木Rubber black wood
触体材料 Contact material	黄铜镀银Brass silver-plated

未注公差 tolerances are not noted		TONGRUIJOIN		东莞市通瑞电子科技有限公司					
0~5	±0.10	设计 DESIGNED	名称 PARTNAME	母头 (直式)	材料 MATERIAL		比例 SCALE	1:1	
6~10	±0.15	校对 CHECKED	型号 Model	AD. MT. GX12. 303. NYA	电镀 PLATING		单位 UNIT	mm	
10~50	±0.20	审核 APPROVED	图号 DRAWING NO.		视图 view		版本 REV	A/0	
51~100	±0.25								
100+	±0.25%								