




SPECIFICATIONS




- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer PA66, UL94V-0
PIN Phosphor bronze Tin-plated





版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



PCB LAYOUT



PIN	尺寸 (mm)		
	A	B	C
-02PW	2.50	7.50	5.70
-03PW	5.00	10.00	8.20
-04PW	7.50	12.50	10.70
-05PW	10.00	15.00	13.20
-06PW	12.50	17.50	15.70
-07PW	15.00	20.00	18.20
-08PW	17.50	22.50	20.70
-09PW	20.00	25.00	23.20
-10PW	22.50	27.50	25.70
-11PW	25.00	30.00	28.20
-12PW	27.50	32.50	30.70



任何孔位第1针打K方向

GENERL TOLERANCE		制 图 Mapping	张迎春 2022、09、15			料 号 PART NO.	KH-A25010-11PW		版 本 REV.	A
X.±0.25	X.°±2°		钱岳生 2022、09、15			品 名 TITLE	XH板对板弯针 WAFER DIP TYPE		页 次 SHEET	1/1
.X±0.25	.X°±1°	审 核 Audit	张 名 2022、09、16			客户料号 CUTM. NO.	深圳市金航标电子有限公司			
.XX±0.15	.XX°±0.5°	核 准 Approved								
.XXX±0.10	.XXX°±0.5°	单 位 Units	mm	比 例 SCALE						