







版次 REV	更改单号 Revise No	制图绘图 DESCRIPTION	日期 Date
A			
B			
C			



### 技术参数:

1. 作用温度: -25~+85°C;
2. 额定负载: DC 12V 50mA;
3. 接触电阻: ≤50mΩ;
4. 绝缘电阻: ≥100MΩ;
5. 耐压: AC250V(50Hz)/min;
6. 动作力: 250±50g;
7. 使用寿命: 50000次;
8. 未注尺寸公差参照下面表格。

A	H(高度)
ø6.8	4.3
ø6.8	5.0
ø6.5	6.0
ø6.5	7.0
ø6.3	8.0
ø6.3	8.5
ø6.3	13.0



PCB线路板安装图(±0.1)

5	嵌件	1	H62Y 黄铜 T=0.30	Ag	
4	底座	1	PPA	黑	
3	簧片	1	不锈钢/复合银	Ag	
2	盖板	1	冷轧钢带	Cu/Sn	
1	按钮	1	PPA	黑	
序号	名称	数量	材料	镀层/颜色	备注
1		2			
		3			
		4			
		5			
		6			
		7			

深圳市逸致电子有限公司 Shenzhen Yizhi Electronics Co., LTD				名 称 Denomination:		轻触开关 TACT SWITCH			
未注公差 General tolerance			设计 Design:		型 号 Part no.:			YZA-105	
X. ± 0.20			X° . ± 1°		校对 Check:			单位 Unit: mm	
. X ± 0.15			. X° ± 0.5°		审核 Auditing:			阶段标记 Phase marker	
. XX ± 0.05			. XX° ± 0.1°		批准 Approve:			重量 Weight	
. XXX ±			. XXX° ±					比例 Scale	
								页码 Sheet of	
								版次 REV	
								A/0	