

RoHS

REV.

ECN. #

DESCRIPTION

NAME



DATE

A0

NEW RELEASE

GuoXuetong

07/06/18



Notes:

1. Material:


Housing: High Temperature Thermoplastic
Terminal: Copper Alloy
Shell: Stainless Steel

2. Plating:

Terminal: 30u" Ni Underplated Overall
G/F Plated On Contact Area
80u" Tin Plated On Solder Area
Shell: 30u" Ni Underplated Overall
G/F Plated On Contact Area And older Area

3. Technical Speciality:

Rated Voltage: 30V
Current Rating: 0.5A
Insulation Resistance: 1000M Ω Min.
Contact Resistance: 100m Ω Max.
Withstanding Voltage: 500V DC For 1 Minutes.
Operating Temperature: -40 $^{\circ}$ C ~ +75 $^{\circ}$ C Humidity 80% R.H Max.



RECOMMENDED PCB LAYOUT

TOLERANCE: ± 0.05

SMT SOLDER AREA

COPPER RESTRICTED AREA
1. TOUCH AREA OF CONTACT
TIPS NO ELECTRICAL FUNCTION
2. NO FIRST PCB_LAYOUT
CIRCUITS IN THE AREA

PIN/NO	ASSIGNMENT
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O

MILLIMETERS	INCH
X. ° $\pm 2^{\circ}$	X. ° $\pm 2^{\circ}$
.X ± 0.30	.X ± 0.012
.XX ± 0.20	.XX ± 0.008
.XXX ± 0.10	.XXX ± 0.004
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd.	




东莞市金比莱五金塑胶科技有限公司

DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd

TITLE	1.35H Push-Push Micro-Sim Card	DR		
PART NO.	102032572	CHKD		
PRO J.	PAGE 1/2	UNITS mm	APPD	
SIZE A4	SCALE 1:1	DIS NO.	MS004-000	客户图


Direction of use →



Carrier Tape

Direction of use →


DETAIL B



DETAIL B

NOTES:

- 1、Packing quantity per plate: 1000PCS/Plate
- 2、Loading and packing method



- 3、Total packaging: 10000PCS/Box

The bottom and top of the carton
Pad it with a piece of pearl cotton

BOX

350*350*340mm

10-REEL

packaging tape

label

Part Number	Description	Quantity
303020029	Carrier band (Lucent , PET W=24 PH=20,T=0.3)	204m
303040009	Box (K=K,T=7.0,350*350*340)	1PCS
303060001	PE Bag (T=0.08mm , 730*760*730)	1PCS
303070024	Self-adhesive (W=21.3)	207m
303110001	Beam (K=K , T=7.0,95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180008	REEL (BLUE , 13Inches*24mm , Ø330)	10PCS
102032572	1.35H PUSH-PUSH Micro-SIM CARD<MS004-000>	10000PCS

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co.,Ltd					
X. ° ±2°	X. ° ±2°						
.X ±0.30	.X ±0.012						
.XX ±0.20	.XX ±0.008						
.XXX ±0.10	.XXX ±0.004						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLaiMetal Plastic Technology Co.,Ltd		TITLE		1.35H Push-Push Micro-Sim Card		DR	
		PART NUM.		102032572		CHKD	
		PRO J.	PAGE	2/2	UNITS	mm	APPD
		SIZE	A4	SCALE	1:1	DIS NO.	MS004-000<客户图>