




RoHS

REV.	ECN. #	DESCRIPTION	NAME	DATE
A1	ECN2106010	PRODUCT OPTIMIZATION		2021.06.25
A2	ECN2307001	OPTIMIZE THE WELDING		2023.07.31



RECOMMEND PCB LAYOUT
GENERAL TOLERANCE ±0.05

NOTES:

1. MATERIAL:

Housing: High Temperature Thermoplastic
UL94V-0; Color Black.

Contacts: Phosphor Bronze.

Gold Flash at Solder Tail, 
Selected Gold Flash on Contact Area plating.

Shell: Stainless.

Gold Flash on Contact solder Area
Over Nickel Plating.

2. Electrical Characteristics:

Rated voltage: 5V.

Current rating: 0.5 A.

Operating Temperature: -25°C~+85°C.


Insulation resistance: 1000M ohms min. at 500VDC

Dielectric withstanding voltage: 500 VAC/1minute.

Contact resistance: 100m ohms max.

3. Mechanical characteristics

Mating durability: 5000 cycles at the speed rate of
400~600 cycles/h; Without distortion of plastic and
serious wear and tear in terminal, No signal break.



Pin No.	MICRO SD	
PIN1	DAT2	1P
PIN2	CD/DAT3	2P
PIN3	CMD	3P
PIN4	VDD	4P
PIN5	CLK	5P
PIN6	VSS	6P
PIN7	DAT0	7P
PIN8	DAT1	8P
PIN9	CARD DETECT	

开关插卡状态


CIRCUIT:

CD GROUND



WITHOUT CARD

CD GROUND



CARD INSERTED

MILLIMETERS	INCH
X.° ±2°	X.° ±2°
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004




THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF DONGGUAN JBL
TECH CO., LTD
COPIED OR USED IN ANY MANNER
WITHOUT THE PRIOR WRITTEN CONSENT
OF DONGGUAN JBL TECH CO., LTD



东莞市金比莱五金塑胶科技有限公司
DONGGUAN JBL TECH CO., LTD


TITLE	1.85H P_P TF Card常开一 体式 无柱	DR		
PART NO.	102XXXXX2	CHKD		
PRO J.	PAGE 1/3	UNITS	mm	APPD
SIZE	A4	SCALE	1:1	DIS NO.
TF014-XXX 客户图				

规格说明


		
简码: TF014-010	简码: TF014-01B	简码: TF014-211
料号: 102014492	料号: 102154492	料号: 102014862
电镀: 接触区镀金1U", 焊脚镀金G/F	电镀: 接触区镀金15U", 焊脚镀金G/F	电镀: 接触区镀金1U", 焊脚镀金G/F
滑块: LOCK导出角79°	滑块: LOCK导出角79°	滑块: LOCK导出角62°

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD									
X. °	±2°	X. °	±2°										
. X	±0. 30	. X	±0. 012										
. XX	±0. 20	. XX	±0. 008										
. XXX	±0. 10	. XXX	±0. 004										
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DONGGUAN JBL TECH CO., LTD COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DONGGUAN JBL TECH CO., LTD				TITLE		1. 85H P_P TF Card常开一体式 无柱		DR					
				PART NO.		102XXXXX2				CHKD			
				PRO J.		PAGE	2/3	UNITS	mm	APPD			
						SIZE	A4	SCALE	1:1	DIS NO.		TF014-XXX 客户图	

RoHS




Direction of use



NOTES:

- 1: Packing quantity per plate: 1000PCS/Plate
- 2: Loading and packing method



- 3: Total packaging: 10000PCS/Box

The bottom and top of the carton
Pad it with a piece of pearl cotton

BOX
350*350*340mm

packaging tape
label

Part Number	Description	Quantity
303020054	Carrierband (Black, PS W=24 PH=20)	204M
303040009	Box (K=K, T=7.0, 350*350*340)	1PCS
303060001	PE Bag (T=0.08mm, 730*760*730)	1PCS
303070024	Self-adhesive (W=21.30)	207M
303110001	Beam (K=K, T=7.0, 95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180017	REEL (BLUE, 13Inches*24mm, $\phi 330$)	10PCS
102XXXXX2	1.85H P-P TF Card 常开一体式卡座<TF014-XXX>	10000PCS

MILLIMETERS		INCH		 东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X. °	±2°	X. °	±2°				
.X	±0.30	.X	±0.012	TITLE		1.85H P-P TF Card常开一体式 无柱	DR
.XX	±0.20	.XX	±0.008	PART NO.		102XXXXX2	CHKD
.XXX	±0.10	.XXX	±0.004	PRO J.		PAGE 3/3	UNITS mm
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DONGGUAN JBL TECH CO., LTD COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DONGGUAN JBL TECH CO., LTD				SIZE		A4	SCALE 1:1
				DIS NO.		TF014-XXX	客户图