


SYMB	REVISIONS	DATE	APVD.
△			
△			
△			



SPECIFICATION:
1,CURRENT RATING:DC 12V 50mA.
2,DIELECTRIC WITHSTANDING VOLTAGE:
250V AC R.M.S. FOR ONE MINUTE.
3,INSULATION RESISTANCE:100M OHMS MIN.
AT 250V DC
4,CONTACT RESISTANCE:30m OHMS MAX.
5,OPERATING TEMPERATURE:-20°C TO +80°C.
6,OPERATING LIFE:50,000 CYCLES.



CIRCUIT

P.C.B LAYOUT DIMENSION
TOP VIEW

TYPE	TACT SWITCH		TOLERANCE		10				
PART NO	KFC-A06-06B-7.3H		HUP TO 10		±0.2	9			
DATE	2016/07/06		ABOVE 10~50		±0.3	8			
UNITE	mm	PAGE	7/7	ABOVE 50~100	±0.5	7			
SCALE	4:1	VERSION	A	ANGLE	±3°	6			
DRAWN	CHECKED	APVD.	PROJECTION		5	TERMINALS	C2680	2	Ag
					4	BOTTOM	PA66	1	BLACK
					3	STEM	PA66	1	BLACK
					2	CONTACT	C5210	1	Ag
					1	COVER	C2680	1	Sn
NO.	NAME		MATERIAL		QTY:	FINISHING			

YZA-084

深圳市逸致电子有限公司
Shenzhen Yizhi Electronics Co., Ltd