

RoHS

REV.

ECN. #

DESCRIPTION

NAME



DATE

A0







NEW RELEASE

X. F. Wang

2022. 11. 03



3D VIEW

ADD TAP VIEW
SCALE 1:2RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mmUC027-000-X
104628662-X无: BLACK HOUSING
L: BLUE HOUSING
C: ORANGE HOUSING
M: BEIGE HOUSING

NOTES:

1.MATERIAL:

- 1.1 HOUSING: HIGH TEMPERATURE PLASTIC UL94V-0
- 1.2 CONTACT: COPPER ALLOY
- 1.3 SHELL: STAINLESS STEEL
- 1.4 MID PLATE: STAINLESS STEEL

2.FINISH:

- 2.1 CONTACT: G/F PLATING ON CONTACT AREA;
MATTE TIN ON SOLDER TAIL;
NI ALL OVER;
- 2.2 SHELL: Ni 50u" MIN. UNDER PLATED OVER ALL;
- 2.3 MID PLATE: CLEAN

3.ELECTRICAL:

- 3-1. CURRENT RATING: 3.0A MAX
- 3-2. INSULATION RESISTANCE:
100 MEGAOHMS MIN.
- 3-3. DIELECTRIC WITHSTANDING VOLTAGE:
100VAC MIN.
- 3-4. LOW LEVEL CONTACT RESISTANCE:
INITIAL 40mΩ MAX.
AFTER 50mΩ MAX.

4.MECHANICAL CHARACTERISTICS:

- 4-1. MATING FORCE: 5~20N
- 4-2. UNMATING FORCE: 8~20N(INITIAL);
6~20N(AFTER TEST);
- 4-3. DURABILITY: 5000 MATING CYCLES.
- 4-4. OPERATING TEMPERATURE: -40°C TO +75°C

MILLIMETERS	INCH
X. ° ±2°	X. ° ±2°
.X ±0.30	.X ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF DongGuan JinBiLai
Metal Plastic Technology Co., Ltd
COPIED OR USED IN ANY MANNER WITHOUT THE
PRIOR WRITTEN CONSENT OF DongGuan
JinBiLai Metal Plastic Technology Co., Ltd

东莞市金比莱五金塑胶科技有限公司

DongGuan JinBiLai Metal Plastic Technology Co., Ltd

TITLE	Type-C 8PIN立贴5.1	DR		
PART NO.	104628662-X	CHKD		
PRO J.	PAGE 1/2	UNITS	mm	APPD
SIZE	A4	SCALE	1:1	DIS NO.
UC027-000-X客户图				

ROHS

A


B

C

D


E

Direction of use




NOTES:


- 1、Packing quantity per plate: 700PCS/Plate
- 2、Loading and packing method



3、Total packaging:7000PCS/Box



The bottom and top of the carton
Pad it with a piece of pearl cotton



Part Number	Description	Quantity
303020184	Carrierband (Lucent, PET W=24 PH=12,T=0.5)	86.4M
303040009	Box (K=K, T=7.0, 350*350*340)	1PCS
303060001	PE Bag (T=0.08mm, 730*760*730)	1PCS
303070024	Self-adhesive (W=21.30)	89.4M
303110001	Beam (K=K, T=7.0, 95*95*290)	4PCS
303130001	Pearl Wool (340*340*18)	2PCS
303180017	REEL (BLUE, 13Inches*24mm, $\phi 330$)	10PCS
104628662-X	Type-C 8PIN立贴5.1	7000PCS

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd					
X. ° ±2°	X. ° ±2°						
.X ±0.30	.X ±0.012						
.XX ±0.20	.XX ±0.008						
.XXX ±0.10	.XXX ±0.004						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF Dongguan JinBiLai Metal Plastic Technology Co.,Ltd		TITLE	Type-C 8PIN立贴5.1			DR	
		PART NUM.	104628662-X			CHKD	
		PRO J.	PAGE	2/2	UNITS	mm	APPD
		SIZE	A4	SCALE	1:1	DIS NO.	UC027-000-X客户图