

地址: 广东省深圳市宝安区松岗沙浦围前海聚英产业园

官网: www.18sz.cn

版本: A0

电话: 0755-23322028

传真: 0755-23322028

邮箱: jyjm@18sz.cn

一、产品简介:

名称: 0B-FGG插头

型号: FGG.0B.307.CLAD


外壳材料: 铜合金镀珍珠铬

针芯材料: 铜合金镀金

二、主要性能参数:

使用环境	室内	温度等级	-40° C, +250° C
冲击	100g, 6ms	机械寿命	>3000次
绝缘电阻	≥5000MΩ (常态下)	震动	15 g [10 Hz - 2000 Hz]
温度	60° C, 95% Max	盐雾	>144h
防水等级	IP50(插合时)	屏蔽	>75dB at 10Mhz, >40dB at 1Ghz

三、编码规则:



四、编码说明:

编号/针芯数	302	303	304	305	306	307	309
孔位排列(公针焊接端)							
接触体直径	0.9	0.9	0.7	0.7	0.5	0.5	0.5
适配导线尺寸(AWG)	22	22	24	24	28	28	28
测试电压(KV mms)	1.00	1.20	0.85	1.00	0.85	0.80	0.60
额定电流(A)	10.0	8.0	7.0	6.5	2.5	2.5	2.0

五、外形尺寸及结构(未注公差: GB/T 1804-m) 单位: mm

