







Circuit 1



PCB LAYOUT



- SPECIFICATIONS
- 1、Current Rating: 2A AC, DC
 - 2、Voltage Rating: 250V AC, DC
 - 3、Temperatuer Range: -25℃~+85℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 1000MΩ Min
 - 6、Withstanding Voltang: 1000V AC/minute
 - 7、Material:Wafer PA66/PA46, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)		
	A	B	C
HY-02AWD	2.00	6.00	2.50
HY-03AWD	4.00	8.00	2.50
HY-04AWD	6.00	10.00	3.50
HY-05AWD	8.00	12.00	5.50
HY-06AWD	10.00	14.00	7.50
HY-07AWD	12.00	16.00	9.50
HY-08AWD	14.00	18.00	11.50
HY-09AWD	16.00	20.00	13.50
HY-10AWD	18.00	22.00	15.50
HY-11AWD	20.00	24.00	17.50
HY-12AWD	22.00	26.00	19.50
HY-13AWD	24.00	28.00	21.50
HY-14AWD	26.00	30.00	23.50
HY-15AWD	28.00	32.00	25.50
HY-16AWD	30.00	34.00	27.50
HY-17AWD	32.00	36.00	29.50
HY-18AWD	34.00	38.00	31.50
HY-19AWD	36.00	40.00	32.50
HY-20AWD	38.00	42.00	35.50

3A以上

GENERAL TOLERANCE		制 图 DRAWING	H Y			料 号 PART NO.	HY-NAWD	版 本 REV.	A
X.±0.25	X.±2°					品 名 TITLE	HY弯针	页 次 SHEET	1/1
.X±0.20	.X±1°	审 核 CHECK	L P J			客户料号 CUTM. NO.			
.XX±0.15	.XX±0.5°	核 准 APPROVAL				L Z W			
.XXX±0.10	.XXX±0.5°	单 位 UNITS	MM	比 例 SCALE	1:1				深圳市富港科技有限公司