





Specification


- 1 Current Rating :0.5A.
- 2 Voltage Rating :DC 5V
- 3 Ambient Temperature Range : $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$
- 4 Ambient Humidity Range :95% R.H. Max.
- 5 Contact Resistance:100m Ω max.
- 6 Insulation Resistance:1000M Ω min./500VDC
- 7 Durability:5,000 cycles




RECOMMEND PCB LAYOUT

RECOMMEND TOLERANCE: $\pm 0.05\text{MM}$

FRAME OF CONNECTOR: - - - - -



pin number	pin name
G1	switch
pin 8	RSV
pin 7	D0
pin 6	VSS
pin 5	SCLK
pin 4	VDD
pin 3	DI
pin 2	CS
pin 1	RSV



STEP III PUSH SHELL (C1/C2 SWITCH LOCK)

③	Shell	—	1	SUS	Ni Plated	—
②	Terminal	—	9	Phosphor Bronze	Sn Plated	—
①	Housing	—	1	Thermoplastic	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	JKUN.LU	2018/8/1					
CHECKED				TITLE:	TF		
APPROVALS				PART NO.	TF-06A		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.25					
	5~10	±0.20					
	~ 5	±0.15					
		±2'	DRAWING NO.		SHEET 1 OF 1		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			