






1	2	3	4	5	6	7	8	9	10	11	12	13	14																																																								
A																																																																					
B																																																																					
C																																																																					
D																																																																					
E																																																																					
F																																																																					
G																																																																					
H																																																																					
I																																																																					
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td>日期</td><td>修改者</td><td colspan="2">摘要</td><td>版本</td></tr> <tr><td></td><td></td><td colspan="2"></td><td></td></tr> <tr><td></td><td></td><td colspan="2"></td><td></td></tr> </table>														日期	修改者	摘要		版本																																																			
日期	修改者	摘要		版本																																																																	
 <u>CIRCUIT DIAGRAM</u>																																																																					
																																																																					
																																																																					
																																																																					
<u>P.C.B. SOLDER LAND DIMENSION</u>																																																																					
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td>3</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>2</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>1</td><td colspan="2">KAN3444M-0181A</td><td>160±30</td><td>40↑</td><td>1.8</td><td>黑色</td><td>黑色</td><td>0.12±0.10</td><td>10万次以上</td><td colspan="4">规格书-002</td></tr> <tr> <td>序号</td><td colspan="2">型号</td><td>克力(g)</td><td>回力(g)</td><td>H(mm)</td><td>手柄色</td><td>底座色</td><td>行程(mm)</td><td>寿命</td><td colspan="4">服从规格</td></tr> </table>														3														2														1	KAN3444M-0181A		160±30	40↑	1.8	黑色	黑色	0.12±0.10	10万次以上	规格书-002				序号	型号		克力(g)	回力(g)	H(mm)	手柄色	底座色	行程(mm)	寿命	服从规格			
3																																																																					
2																																																																					
1	KAN3444M-0181A		160±30	40↑	1.8	黑色	黑色	0.12±0.10	10万次以上	规格书-002																																																											
序号	型号		克力(g)	回力(g)	H(mm)	手柄色	底座色	行程(mm)	寿命	服从规格																																																											
绘图 (DRAW)				未标注公差尺寸		型号: (DRAWING NO)		TS-034-FSMH-H1.8		品名: (TITLE)		3*4两脚防水梅花柄开关																																																									
校对 (CHECK)				METRIC TOLERANCE		图档: (DWG ID)				时间: TIME		2021.09.19		页次: (PAGE)	1/1																																																						
核准 (APPR)				.0 ±0.30										版本: (REV)	A0																																																						
				.00 ±0.20																																																																	
				.000 ±0.10																																																																	
						投影法: (PROJECT)				材质: (MATERIAL)				比例: (SCALE)	FIT																																																						
														单位: (NUITS)	mm																																																						
														版本: (REV)	A0																																																						
