







	Pitch dimension			Nominal dimension					
variable range	over 0 ~ 6	over 6 ~ 10	over 10 ~ 24	over 0 ~ 30	over 30 ~ 60	over 60 ~ 100	over 100 ~ 150	150	
Tolerance	±0.1	±0.15	±0.25	±0.20	±0.3	±0.5	±0.7	±1	0.05/10

2		基座	PA66 UL94V-0	1	绿色	
1		方针	黄铜 H65	N	镀镍锡	
序号	代号	名称	材质	数量	电镀/颜色	备注

技术参数:			
过压类别/Overvoltage Category/污染等级/Pollution Degree	III/3	III/2	II/2
额定电压/电流/Rated Voltage(V)/Current(A)	/	250V/8A	/
耐电压/Withstanding voltage(V/1Min)	2000		
额定冲击电压(Rated impulse voltage) [KV]	4.0		
绝缘电阻/Insulation resistance	常态≥500MΩ		
接触电阻/Contact resistance	<20mΩ		
单PIN插针保持力/Binding force(N)	>25N		
波峰焊/Welding welding	260°C±5°C		
间距/Pitch(mm)/线数范围/Poles	5.08/N=02~12P		
使用温度范围/Operating temperature(°C)	-40~+105		
相对湿度/Relative humidity	湿度≤95%(温度+40°C)		
符合RoHS环保要求/Conform to RoHS	Yes		

 深圳市韩下电子有限公司				NAME: 插拔式接线端子(插座)		
				NAME: HX-HE430-5.08-2P		
设计	黄彬	工艺		视角		图幅:A4
审核	张伟	标准化		比例	1:1	单位:mm
批准	罗小春	日期	2022.8.30	页面	1/1	版本/次:B/0