





1	2	3	4	5	6	7	8
H	G	F	E	D	C	B	A
					标记	处数	变更文件及描述
					签字	日期	Pitch=5.08mm
							Poles L(mm) A(mm)
					02	5.08	10.16
					03	10.16	15.24
					04	15.24	20.32
					05	20.32	25.4
					06	25.4	30.48
					07	30.48	35.56
					08	35.56	40.64



	Pitch over 0 ~ 6	dimension over 6 ~ 10	over 10 ~ 24	over 24 ~ 30	Nominal dimension over 30 ~ 60	over 60 ~ 100	over 100 ~ 150	over 150	
variable range	0.1	±0.15	±0.25	±0.20	±0.3	±0.5	±0.7	±1	0.05/10
Tolerance	±0.1	±0.15	±0.25	±0.20	±0.3	±0.5	±0.7	±1	0.05/10

4		插脚	H62 Y2	N	镀镍锡	
3		压线框	H59	N	镀镍	
2		基座	PA66 UL94V-0	1	绿色	
1		螺钉	22A	N	镀三价五彩锌	
序号	代号	名称	材质	数量	电镀/颜色	备注

 深圳市韩下电子有限公司 NAME: 固定式接线端子	NAME: HX-HB612-5.08-2P	
	设计	黄彬
审核	张伟	工艺 标准化
比例	1:1	图幅:A4 单位:mm
批准	罗小春	日期 2022.4.15 页面 1/1 版本/次:A/0