





RoHS
Compliant
2011/65/EU





REV.	ECN NO OR DESCRIPTION	REVISED	DATE

A





SECTION A-A

B



C



PCB LAYOUT

NOTE:

1. MATERIAL:
HOUSING: LCP WITH 30% GF, UL 94V-0,
BLACK COLOR.
TERMINAL: COPPER ALLOY.

2. ELECTRICAL:
CURRENT RATING:1.5 AMPERE PER CONTACT
CONTACT RESISTANCE:30 MILLIOHMS MAX
INSULATION RESISTANCE:1000 MEGOHMS MIN
DIELECTRIC WITH STANDING VOLTAGE:500 VDC
OPERATING TEMPERATURE:−25°C ~ +85°C

DIM A	PART NO.	塑胶区别
1.0	SATA-009-M22S1BY-A	中间有缺口/七个孔
1.2	SATA-009-M22S1BY-B	七个孔
1.6	SATA-009-M22S1BY-C	七个孔
0.8	SATA-009-M22S1BY-D	七个孔


UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS:	ANGLES:	TITLE	SATA 7+15P夹板公座	
X :±0.25	X.X :±1°	DWN	xiong	PART NO. SATA-009-M22S1BY-X
X.X :±0.20	X.XX :±0.15	CHKD	lee	SCALE:1:1
		APVD	wang	UNIT: mm SIZE: A4 SHEET:10F 1 REV: A4 CUSTOMER COPY



RoHS
Compliant
2011/65/EU



A



最上层放一个空吸塑盒



每叠=20盘

PE膜“工”字型缠绕

4叠=80盘

△说明:

1. 一盘吸塑盒=60 PCS
2. 每叠20盘=60 PCS/盘*20
=1200 PCS
3. 一箱=4叠=每叠1200 PCS *4
=4800 PCS/箱



UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS: ANGLES:
X :±2°
X :±0.25 X.X :±1°
X.X :±0.20
X.XX :±0.15

TITLE	SATA 7+15P夹板公座		
DWN	xiong	PART NO. SATA-009-M22S1BY-X	
CHKD	lee	SCALE:1:1	UNIT: mm
APVD	wang	SIZE: A4	SHEET:1OF 1
		REV: A4	

CUSTOMER COPY