



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

NOTES:




Rating: 0.5A 30V DC

Contact: Resistance 100mΩ Max.

Operating temperature: -20°C~70°C



Operating force: 3-20N

Operating Life: 5,000cycles



DC MATE PLUG

PIN	Item number
Ø2.0	DC-012-N200
Ø2.5	DC-012-N250



6	PIN	1	HPB50-1	MB:Cu Cu/Sn PLATE
5	TIP SPRING	1	SUS II=0.2	MB:Cu Cu/Sn PLATE
4	SHUNT SPRING1	C2680 T=0.3	MB:Cu Cu/Sn PLATE	
3	RERMDNAI	1	C2680 T=0.3	MB:Cu Cu/Sn PLATE
2		1		BLACK
1	HOUSING	1	PBT UL 94V-0	BLACK
LTR	PART NAME	OTY	MATER1AL	

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.25 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	PHONE JACKES
DWN	xiong
CHKD	lee
APVD	wang
PART NO.	DC-012-NXXX
SCALE:1:1	UNIT: mm
SIZE: A4	SHEET:10F 1
REV: A4	

CUSTOMER COPY