




RoHS
Compliant
2011/65/EU




REV.	ECN NO OR DESCRIPTION	REVISED	DATE


A




B



C



D



NOTE:

1. MATERIAL:
HOUSING: LCP WITH 30% CF, UL 94V-0, BLACK COLOR.
CONTACTS: PHOSPHOR BRONZE.
BORAD LOCK: COPPER ALLOY.
2. FINISH:
CONTACTS: GOLD FALSH PLATED ON CONTACT AREA, [100 μ] MIN..
BRIGHT-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT
UNDERPLATED [50 μ] MIN.. NICKEL.
BORAD LOCK: [100 μ] MIN. TIN OVER[50 μ]MIN. NICKEL PLATED.

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD	
DECIMALS:	ANGLES:	TITLE	SATA 7+15P长体单排180度DIP PC 2.5 带鱼叉
X :±0.25	X.X :±1°	DWN	xiong
X.X :±0.20	X.XX :±0.15	CHKD	lee
		APVD	wang
			SCALE:1:1 UNIT: mm
			SIZE: A4 SHEET:1OF 1 REV: A4
			CUSTOMER COPY



RoHS
Compliant
2011/65/EU



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

A


1-1 将SATA 产品整齐的装入真空盒底盒内。

1-2 将真空盒盖盖在装有成品的底盒上，以免产品漏失。


备注：

每盘装成品50PCS


真空壳规格：长245*宽245*高10CM



2-1 每箱分2扎装，每层放盖子1PCS：每扎共20盘，用PE膜扎成一扎；每箱的数量小计：
 $(50*20) + (50*20) = 2000CS$




3-1 将2摞成品依次放入纸箱内。备注：
纸箱规格：长52*宽26*高22CM K=A



B

4-1 纸箱开口处以透明胶带贴合。

4-2 若有未装满的零数箱,必须以缓冲材塞满。



UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:	ANGLES:	TITLE	SATA 7+15P长体单排180度DIP PC 2.5 带鱼叉
X :±0.25	X.X :±1°	DWN	xiong PART NO. SATA-010-F22S1BY-A
X.X :±0.20	X.XX :±0.15	CHKD	lee SCALE:1:1
		APVD	wang UNIT: mm
			CUSTOMER COPY
			SIZE: A4 SHEET:1OF 1 REV: A4