





REV.	DESCRIPTION	ECN NO.	NAME	DATE

SPECIFICATIONS
Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
B254YP-ZS01P-PC032	1	0.00	2.54
B254YP-ZS02P-PC032	2	2.54	5.08
B254YP-ZS03P-PC032	3	5.08	7.62
B254YP-ZS04P-PC032	4	7.62	10.16
B254YP-ZS05P-PC032	5	10.16	12.70
B254YP-ZS06P-PC032	6	12.70	15.24
B254YP-ZS07P-PC032	7	15.24	17.78
B254YP-ZS08P-PC032	8	17.78	20.32
B254YP-ZS09P-PC032	9	20.32	22.86
.....			
B254YP-ZS40P-PC032	40	(PIN-1)X2.54	(PIN)X2.54

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN[®] 		
DIM.	TOL.	TITLE: 2.54FH H8.5 2xnPin 180度 Y型 PC3.2 6T							
X.	±0.30	DWG. NO.: B254YP-ZSXP-PC032			CHECKED: MAX				
X.X	±0.20								
X.XX	±0.10	PART NO.: B254YP-ZSXP-PC032			DRAWN: ELLA				
GENERAL ANGLE:									
X.°	±5°	APPROVED: WILL							
X.X°	±1°								
X.XX°	±0.5°								
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn			