










RECOMMENDED P.C.B. LAYOUT(T=1.60)
PCB TOLERANCE ±0.05mm

REV.	ECN NO OR DESCRIPTION	REVISED	DATE




- 1.MATERIAL SPECIFICATION,
1-1.HOUSING:THERMOPLASTIC,HIGH TEMP,UL 94V-0 ; BLACK;
1-2.COVER:THERMOPLASTIC,HIGH TEMP,UL 94V-0 ; BLACK;
1-3.CONTACT:COPPER ALLOY T=0.2;
1-4.HOOK:COPPER ALLOY T=0.3;
2.PLATING SPECIFICATION,
2-1.CONTACT:
UNDER PLATING:Ni 50u" Min PLATED OVER ALL;
CONTACT AREA: SEE TABLE;
SOLDER TAIL: MATTE TIN 100u" Min PLATED ;
2-2.HOOK: MATTE TIN 100u" Min PLATED OVER Ni 50u" Min.
3.RoHS OR HF COMPLIANT


UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	SATA 7PIN SMT CONN		
X :±0.25	X :±2°	DWN	xiong	PART NO. SATA-008-M07S1BR-A	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.15		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					




REV.	ECN NO OR DESCRIPTION	REVISED	DATE




产品图示




1. 卷盘贴标签




2. 8盘产品叠层



3. 套PE袋



5. 三角板 (4pcs)



4. 在底部和最上面各放一块纸板


NOTE:

1. QUANTITY/REEL:350 PCS

数量/卷:350 PCS

QUANTITY/INNER CARTON:350 X 8 = 2800 PCS

数量/箱: 350 X 8 = 2800 PCS



UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	SATA 7PIN SMT CONN		
X :±0.25	X :±2°	DWN	xiong	PART NO.SATA-008-M07S1BR-A	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.15		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					