









PCB MOUNTING HOLES
BOTTOM VIEW
(TOLERANCE: ±0.05)

ELECTRICAL

VOLTAGE RATING:20V DC (R.M.S)

CURRENT RATING:10A

CONTACT RESISTANCE:30mΩ MAX.

INSULATION RESISTANCE:100 MΩ MIN.


DIELECTRIC WITHSTAND VOLTAGE:500V AC (R.A.M)

TEMPERATURE RANGE:-25°C TO +85°C

MATERIALS & PLATING: SEE THE TABLE BELOW.

ORDERING INFORMATION:

PIN	Item number
Ø1.65	DC-007B-N165
Ø2.00	DC-007B-N200
Ø2.50	DC-007B-N250



SCHEMATIC

6	GROUND	1	SUS 301 0.15t	
5	SHELL	1	SPCC 0.4t	NI- PLATING
4	TERMINAL	1	SUS 301 0.3t	
3	PIN	1	H59	Ag-PLATING
2	SPRING	1	COPPER ALLOY 0.3t	CuSn-PLATING
1	HOUSING	1	PA9T UL 94V-0	BLACK
LTR	PART NAME	QTY	MATERIAL (THICK,COLOR)	REMARK

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:	ANGLES:
X :±0.30	X :±2°
X.X :±0.25	X.X :±1°
X.XX :±0.15	

TITLE	PHONE JACKS			
DWN	xiong	PART NO. DC-007B-NXXX		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY