





1 2 3 4 5 6 7 8



	Pitch dimension			Nominal dimension					
variable range	over 0 ~ 6	over 6 ~ 10	over 10 ~ 24	over 0 ~ 30	over 30 ~ 60	over 60 ~ 100	over 100 ~ 150	over 150	
Tolerance	±0.1	±0.15	±0.25	±0.20	±0.3	±0.5	±0.7	±1	0.05/10

1 标记 处数 变更文件及描述 签字 日期
2 3 4 5 6 7 8

2	基座	PA66 UL94V-0	1	绿色	
1	方针	黄铜 H65	N	镀镍锡	
序号	代号	名称	材质	数量	电镀/颜色
技术参数:					
过压类别/Overvoltage Category/污染等级/ Pollution Degree		III/3	III/2	II/2	
额定电压/电流/Rated Voltage(V)/Current(A)	/	250V/8A	/		
耐压/Withstanding voltage(V/1Min)		2000			
额定冲击电压(Rated impulse voltage) [KV]		4.0			
绝缘电阻/Insulation resistance		常态≥500MΩ			
接触电阻/Contact resistance		<20mΩ			
单PIN插针保持力/Binding force(N)		>25N			
波峰焊/Welding welding		260°C±5°C			
间距/Pitch(mm)/线数范围/Poles		5.08/N=02~12P			
使用温度范围/Operating temperature(°C)		-40~+105			
相对湿度/Relative humidity		湿度≤95%(温度+40°C)			
符合RoHS环保要求/Conform to RoHS		Yes			

	NAME: 插拔式接线端子(插座)	NAME: HX-HE430-5.08-3P	
		设计 黄彬	工艺
审核 张伟	视角		图幅:A4
	比例	1:1	单位:mm
批准 罗小春	日期	2022.8.30	版本/次:B/0
	页面	1/1	