





REV.	ECN NO OR DESCRIPTION	REVISED	DATE



NOTES:

Rating: 0.5A 30V DC


Contact: Resistance 100mΩ Max.

Operating temperature: -20°C~70°C



Operating force: 3-20N

Operating Life: 5,000cycles

PIN	Item number	current
Ø1.0	DC-002-A10	1A
Ø1.3	DC-002-A13	1A
Ø1.65	DC-002-A165	1A



DC MATE PLUG



6	PIN	1	HPB50-1	MB: Cu Cu/Sn PLATE
5	TIP SPRING	1	SUS II=0.2	MB: Cu Cu/Sn PLATE
4	SHUNT SPRING	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
3	RERMDNAI	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
2		1		BLACK
1	HOUSING	1	PBT UL 94V-0	BLACK
TR	PART NAME	1	QTY	MATER1AL

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.25 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	PHONE JACKES			
DWN	xiong	PART NO. DC-002-AXX		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY