










Technical requirements	
Characteristic impedance	50 Ω
Frequency range	0-3GHZ
Contact resistance	
Inner conductor	$\leq 3m\Omega$
Outer conductor	$\leq 2m\Omega$
Insulated resistance	$\geq 5000M\Omega$
Salt spray time	48H
Separation force	$\geq 0.28N$
Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc	



PCB.WELDING DRAWING (TOLERANCE:±0.05)

1	半螺铜座	1	黄铜	镀金
2	平头母针	1	黄铜	镀金
3	绝缘体	1	PTFE	
序号	名称	数量	材料	备注
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.30	X':±5°	PART NO. ASMA-KE-ZH135	TITLE: 正脚-半螺内孔-H13.5-P	
X.X:±0.25	X.X':±1°			
X.XX:±0.15				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		SCALE N:A
				SHEET 1/1