

A	Dept	晨翔2.54双排母，弯针，黑色，半金镍，2*40P H=8.5mm	REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED	A
	Qty		A	NEW RELEASE	WPY 06/05/25'	~		
	DC	1						
	ED	1						
	IE	1						
	ISO	1						
B	PD	1						B
	R&D	1						
	SD	1						
	QA	1						
C	QC	1						C
	QE	1						
晨翔料号：DS1024-2x40R2 0.60*0.4t 102.1±0.3 2.54±0.1 99.06±0.25 8.50 5.00 12.6 2.54 3.5 2.54 99.06±0.25 Ø1.02 PCB孔位尺寸参考 公差: ±0.05			备注: 1. 电性说明: 1.1 接触阻抗: 20毫欧最大 1.2 耐压: 600伏交流电一分钟 1.3 绝缘阻抗: 1000兆欧最小 1.4 额定电流: 3安 1.5 额定电压: 250V AC 2. 环境特性: 2.1 工作温度: -40~+105° C 3. 材料: 3.1 端子: 铜合金, 镍底镀金 3.2 胶芯: PBT, 黑色, 阻燃					B
D								D
E								E
F								F
G								G
H								H

晨翔电子有限公司

CONNFLY CONNFLY ELECTRONIC CO. LTD