









RECOMMENDED PCB LAYOUT 1
(GENERAL TOLERANCE IS ± 0.05)



RECOMMENDED PCB LAYOUT 2
(GENERAL TOLERANCE IS ± 0.05)



NOTE:

1. MATERIAL:

- ① 1.1. HOUSING: THERMOPLASTIC, COLOR: BLACK, UL 94V-0;
- ② 1.2. CONTACT: COPPER ALLOY, $T=0.10\text{mm}$;
- ③ 1.3. SHELL: COPPER ALLOY, $T=0.12\text{mm}$.

2. FINISH:

- 2.1. CONTACT: GOLD FLASH PLATED ON MATING AREA, GOLD FLASH ON SOLDER TAILS, NICKEL UNDER PLATED OVER OF THE ALL;
- 2.2. SHELL: GOLD FLASH ON THE ALL, NICKEL PLATED UNDER.

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.: ± 0.50	X': $\pm 2^\circ$	PART NO. ARF-001	TITLE: Ultra Small Surface Mount Coaxial CONN. USS RF SERIES		
X.X: ± 0.10	X.X': $\pm 1^\circ$				
X.XX: ± 0.05		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm				
MATERIAL	---	CHED: Olivia		SCALE	SHEET
FINISH	---	APPD: Ava		N/A	1/1